PRX Systems: For a total filtration solution

When a complete filtration solution is your goal, a LAKOS PRX System is the answer.

A total solution requires more than just getting the solids out of your process. Addressing the tough demands of the process industries, the LAKOS PRX System is designed and engineered to give a total solution - enabling you to get the solids out of your fluid, out of the separator and out of your facility.

Featuring the centrifugal-action performance of the LAKOS Separator, the fully engineered PRX System offers your choice of purging and solids-handling options along with complete electrical controls, all mounted on a modular support stand.

Fully-accessible LAKOS Separator

Industrial-quality JPX-Series Separators with patented Vortube and Swirlex slots. Weld-on flanges and ASME code construction options available.

Choice of inlet profile

Specify up, down or either side to accommodate desired installation piping scheme.

Automatic purging options

Pneumatic pinch valve or the patented LAKOS Purge Liquid Concentrator.

Solids-handling options

Drum shroud decant system or rollaway solids collection hopper offer convenient options for handling purged solids.

Engineered support stands

Modular for easier and more affordable shipping; two styles to match separator size. Carbon steel.

Value-added accessories

Included with all PRX Systems: Inlet and outlet spools with couplings; inlet and outlet pressure gauges with petcock valves; full-port manual isolation valve.





Description

Components

Dimensions

Specifications

Warranty

Flow range: 4 - 12,750 U.S. gpm (1 - 2895 m³/hr)

Custom system configurations and systems with pumps and other components available; contact factory.





Dimensions

Limited Warranty

All products manufactured and marketed by this corporation are warranted to be free of defects in material or workmanship for a period of at least one year from date of delivery. Extended warranty coverage applies as follows:

All LAKOS Separators: Five year warranty

All other components: 12 months from date of installation; if installed 6 months or more after ship date, warranty shall be a maximum of 18 months from ship date.


If a fault develops, notify us, giving a complete description of the alleged malfunction. Include the model number(s), date of delivery and operating conditions of subject product(s). We will subsequently review this information and, at our option, supply you with either servicing data or shipping instruction and returned materials authorization. Upon prepaid receipt of subject product(s) at the instructed destination, we will then either repair or replace such product(s), at our option, and if determined to be a warranted defect, we will perform such necessary product repairs or replace such product(s) at our expense.


This limited warranty does not cover any products, damages or injuries resulting from misuse, neglect, normal expected wear, chemically-caused corrosion, improper installation or operation contrary to factory recommendation. Nor does it cover equipment that has been modified, tampered with or altered without authorization.

No other extended liabilities are stated or implied and this warranty in no event covers incidental or consequential damages, injuries or costs resulting from any such defective product(s).

Lakos Separators are manufactured and sold under one or more of the following U.S. Patents: 3,289,608; 3,512,651; 3,568,837; 3,701,425; 3,947,364; 3,963,073; 4,027,481; 4,120,795; 4,123,800; 4,140,638; 4,147,630; 4,148,735; 4,305,825; 4,555,333; 5,320,747; 5,338,341; 5,368,735; 5,425,876; 5,571,416; 5,578,203; 5,622,545; 5,653,874; 5,894,995; 6,090,276; 6,143,175; 6,167,960; 6,202,543; Des. 327,693; and corresponding foreign patents, including 600 12 329.4-08 (Germany) and EP 1 198 276 B1 (EU); other U.S. and foreign patents pending.

1365 North Clovis Avenue Fresno, California 93727 USA Telephone: (559) 255-1601 www.lakos.com info@lakos.com





| LAKOS ———————————————————————————————————— | |
|--|-------------------------------------|
| | |
| Solids Purge | |
| Pneumatic ———————————————————————————————————— | |
| Purge Diffuser | |
| | L LAKOS Auto-Purge Controller |
| LAKOS SDS System | LAKOS PRX Stand |
| | |

Models PRX-0004 through PRX-0130 Stand footprint is 10" square (254 mm); height is 89" (2261 mm), (without separator). Total space requirement will depend on solids collection options.

| Model | Length (A) | | Width (B) | | Height (C)* | |
|----------|------------|------|-----------|------|-------------|------|
| | in. | mm | in. | mm | in. | mm |
| PRX-0200 | 40" | 1016 | 67" | 1702 | 115-1/4" | 2927 |
| PRX-0285 | 51" | 1295 | 67" | 1702 | 121-3/4" | 3092 |
| PRX-0450 | 65-3/8" | 1661 | 67" | 1702 | 130-1/2" | 3315 |
| PRX-0650 | 74-7/8" | 1902 | 67" | 1702 | 143" | 3632 |
| PRX-1160 | 89-1/2" | 2773 | 67" | 1702 | 162-5/8" | 4131 |

*Add 13-1/4" (337 mm) to overall height for systems with Purge Liquid Concentrator option.

Specifications

| Model | Flow Range | | Inlet/Outlet | Purge Size |
|----------|--------------|--------------------|-------------------|-------------|
| | U.S. gpm | m ³ /hr | Grooved Coupling* | Male N.P.T. |
| PRX-0004 | 4 - 10 | 1-2.5 | 1/2" | 1" |
| PRX-0010 | 10 - 20 | 2.5-4.5 | 3/4" | 1" |
| PRX-0016 | 16 - 30 | 4-7 | 1" | 1" |
| PRX-0028 | 28 - 45 | 7-10 | 1-1/4" | 1-1/2" |
| PRX-0038 | 38 - 65 | 9-15 | 1-1/2" | 1-1/2" |
| PRX-0060 | 60 - 100 | 14-23 | 2" | 1-1/2" |
| PRX-0085 | 85 - 145 | 19-33 | 2-1/2" | 1-1/2" |
| PRX-0130 | 130 - 225 | 30-51 | 3" | 1-1/2" |
| PRX-0200 | 200 - 325 | 45-74 | 4" | 1-1/2" |
| PRX-0285 | 285 - 525 | 65-120 | 4" | 1-1/2" |
| PRX-0450 | 450 - 825 | 102-187 | 6" | 1-1/2" |
| PRX-0650 | 650 - 1200 | 150-275 | 6" | 1-1/2" |
| PRX-1160 | 1160 - 2150 | 265-490 | 8" | 1-1/2" |
| PRX-1850 | 1850 - 3400 | 420-775 | 10" | 2" |
| PRX-2650 | 2650 - 4900 | 600-1115 | 12" | 2" |
| PRX-4200 | 4200 - 7800 | 950-1775 | 16" | 3" |
| PRX-6700 | 6700 - 12750 | 1520-2895 | 20" | 3" |

*PRX-0004 and PRX-0010 are male N.P.T.

